

FluidPRO™ EV-1 Exhaust Ventilation System

Add safety and professionalism to your facility with the EV-1 Exhaust Ventilation System.

The EV-1 is highly portable and practical. It is designed to efficiently and quickly extract harmful gases out of any shop.

Simple Operation – spring loaded column for easy height adjustment, durable locking casters for excellent mobility, includes dual exhaust adapter (does not include hoses & nozzles for dual exhaust, kit required – see accessories section)

Enhanced Shop Environment – provides safer & healthier work environment, 110V 3/4 HP motor for HI-FLOW positive pressure ventilation



**EV-1
Exhaust Ventilation System**

P/N 435-80001-00

Specifications

Dimensions	40 in x 22 in x 22 in (102 cm x 56 cm x 56 cm) (H x W x D)
Total Weight	73 lb (33 kg)
Motor	110 VAC (0.75 HP)
Hose	40 ft (12 m) long; 5 in (12.7 cm) diameter
Electrical Outlet	Minimum 6 Amp
A-Weighted Surface Noise Rating	Corrected LpA = 73 dB (A)
Working Temperature	23° to 120°F (-5° to 49°C)
Fuses	Qty (2) 16 Amp time delayed; 0.39 in x 1.49 in (10 mm x 38 mm)
Warranty	1 Year Parts & Labor

Transmission Accessories

ATX Flush Canister, In-Line, 14 oz. P/N 300-80061-00

Use this in-line, 14 ounce canister when flushing a sealed transmission. Attaches in-line between the vehicle and machine. Once you add the flush, it is automatically carried into the system with transmission fluid. Will also work with many popular fluid exchange machines.



**ATX Adapter #95
P/N 000-80080-00**
GM Saturn Ion 2.2 Liter
(2003+)

**ATX Adapter #96
P/N 000-80081-00**
GM Saturn Ion 2.2 Liter
(2003+) vehicle.

ATX-2 Bypass Adapter Hose P/N 300-80052-00

The Bypass Adapter Hose is used to connect the cooler lines together while moving the vehicle.

ATX Adapter #93 P/N 000-80082-00

Ford F250 & F350 (2005+)



**ATX Adapter #47
P/N 000-80085-00**
Saab 93 Sport, 2003-2008



Quick Disconnect Tool Set (Four sizes included: 3/8 in., 1/2 in., 5/8 in., 7/8 in.), P/N 026-80361-00

Unique stainless steel design tool makes quick work of those Jiffy-Tite fittings. Eliminates the need to remove the spring clip. Losing and/or damaging springs is no longer a problem. Hinged to slip over the tube and closes around the tube; slide into and open the spring clip for easy removal of the tube from the fitting. Saves valuable time!

